

Molded of densely laminated fiberglass-reinforced plastic (FRP), Leopold wash-water troughs are corrosion-resistant and constructed for maintenance-free durability and long service life. All mounting brackets, hardware, and stabilizers are stainless steel.

Reinforced for strength and stiffness

Leopold FRP wash-water troughs are designed and manufactured for rigidity and dimensional accuracy. Proportioned for excellent beam strength, Leopold FRP wash-water troughs have triangular-shaped,



Leopold® Fiberglass Wash-Water Troughs

longitudinal stiffeners integrally molded into the exterior sidewall for longitudinal rigidity.


Fiberglass thickness is at least 1½ times the nominal thickness at locations of supports such as saddles, as well as at end flanges and blind ends. One-inch horizontal stiffener bars on 2-foot centers enhance the structural rigidity.

Resin-rich surface for even flow

The inner surfaces of Leopold troughs are smooth, and resin-rich-coated to minimize flow resistance. The top edges of each trough section are level and parallel to the specified tolerances to help uniformly match a still water surface at the desired overflow elevation.

Easy, economical installation

Leopold troughs require no costly forming work. They are available with fixed, adjustable flanged ends, or with integrally mounted water stops. Adjustable V-notch or straight-edge weir plates are also available. The weir plates are made of maintenance-free fiberglass-reinforced plastic, match-die molded to ensure excellent dimensional accuracy.







www.GlomacAmerica.com





Reduced maintenance

Consider the Many Clari-Vac Floating Sludge Collector Advantages Lower disposal costs From the heavier solids concentration Greater productivity Removal is fast-up to 12 fpm

Quick, Simple Valve Priming Priming the siphon valves and setting optimal flow control is quick and simple, taking less than two minutes with a standard wet-dry shop-vac.







Sludge Return Dense sludge is d return channel the











Leopold Clari-Vac Floating Sludge Collector

Simply Powerful Sludge Removal for Water and Wastewater Treatment Plants




Reliable, Proven Performance

For more than three decades the Leopold Clari-Vac floating sludge collector has proven the optimum choice as a sludge collector for a wide variety of water and wastewater treatment facilities. The Clari-Vac floating sludge collector removes material faster, produces a higher solids content, lowers sludge disposal costs, drastically reduces power costs, and virtually eliminates maintenance. Its exceptional performance is another example of how the Leopold concept of engineered simplicity continues to deliver powerful and reliable solutions for the water and wastewater treatment industries.

Engineered Simplicity

The Leopold Clari-Vac floating sludge collector owes its outstanding and reliable performance to its engineered simplicity. Operating on the basic principles of buoyancy and siphon, collection headers on the Clari-Vac submerged sludge collector "vacuum" the solids that have naturally settled and compacted on the tank floor.

Sludge is then siphoned into a separate trough where it is pumped to waste in water plants or returned to secondaries in wastewater activated sludge applications. There are no moving parts under water and all parts except the drive are nonferrous metals to minimize corrosion potential.








Leopold[®] CT2[®] Submerged Sludge Collector

Superbly Simple, Highly Efficient Sludge Removal For Water Treatment Plants



Reliable, Proven Performance


For more than twenty years Leopold CT2 submerged sludge collector systems have quietly done their job . . . delivering reliable operation, low maintenance costs, and good sludge production in hundreds of facilities worldwide. The CT2 submerged sludge collection system, distinguished by its engineered simplicity, takes sludge removal to the next level. By simplifying the water treatment process, the CT2 sludge collection system increases plant efficiency, and reduces both maintenance time and total system operational costs. It's simply powerful sludge removal you fit and forget.

Engineered Simplicity

Engineered simplicity is integral to the design of the Leopold CT2 sludge collection system. It operates on a simple principle and a powerful force: gravity. We've designed a superbly simple but highly efficient process to remove sludge by taking advantage of a differential head. Water pressure in the main tank forces the sludge through the header collector into the outlet piping, and away to the sludge removal trough. Careful selection of smooth-bore piping for the suction header keeps headloss to a minimum for the most efficient sludge removal and low driving head requirements. A simple cable drive moves the suction header across the tank floor at a steady, controlled rate, removing sludge without disturbance. Pumping costs are eliminated and cable drives require far less power.

Fit and Forget

The Leopoid C-12 submerged studge collection system has a fit and forget" quality that not only simplifies the water treatment process, but also reduces system operation costs. The header, locked onto the guide ral and controlled by a programmable operating system, goes where and when you want it. The cable drive pulls the header through the sludge with a positive to the process of the process of the process of the process. and minimal sludge disturbance, removing the sludge without dilution. This reduces sludge volumes and thickening costs, too. And compared to other submerged sludge collectors, the Leopold CT2 submerged sludge collection system is far simpler to maintain because it has a minimal number of moving parts.



Adaptable to a Variety of Plant Requirements

High-Rate Sedimentation



The CT2 sludge collection system can be easily installed or retrofitted into a plate settler or tube settler sedimentation tank. Good quality sludge can then be removed as raw water conditions demand. The CT2 sludge collection system is the optimum choice for flat-bottom tanks or tanks with sloped floor As the suction header glides through the sludge, it removes the settled sludge with minimal dilution and

Multi-Pass Control Options



It sludge collection he feability to meet to compensate for high-solids production water to compensate for high-solid production water t

Laoppia Controls for the C.1.2 studge Collection system can give each plant the flexibility to measure system can give each plant the flexibility to mean basins sludge settles unevenly, with more accumulating in the inlet area than in other areas of the basin. Advanced Leopold controls can be programmed to increase sludge removal at the inlet of the tank to even out the sludge load, providing consistent sludge for thickening and disponal.

to compensate for high-solids-production water with a double header driven by a single cable system. The travel length of the header is designed to draw the desired amount of sludge from the basin where sludge production is greatest. Double headers also accommodate extra-long basin design.

Flexible Installation Design



The Leopold CT2 sludge collection system can be designed to accommodate extra-wide sedimentation anks. And each track can be separately controlled o vary the number of passes and the speed of each